

PRODUCT INFORMATION SHEET

No.	Information	Value and precision
1	Supplier's name or trade mark	CARRIER JAPAN CORPORATION
2	Supplier's model identifier	40VCC73-8FJEE
3	Energy efficiency class for standard Dynamic Range (SDR)	n.a.
4	On mode power demand for Standard Dynamic Range (SDR)	n.a.
5	Energy efficiency class (HDR)	n.a.
6	On mode power demand in High Dynamic Range (HDR) mode	n.a.
7	Off mode, power demand	n.a.
8	Standby mode power demand	n.a.
9	Networked standby mode power demand	n.a.
10	Electronic display category	Other
11	Size ratio	n.a.
12	Screen resolution (pixels)	n.a.
13	Screen diagonal (cm)	n.a.
14	Screen diagonal (inches)	n.a.
15	Visible screen area	n.a.
16	Panel technology used	n.a.
17	Automatic Brightness Control (ABC) available	n.a.
18	Voice recognition sensor available	n.a.
19	Room presence sensor available	n.a.
20	Image refresh frequency rate	n.a.
21	Minimum guaranteed availability of software and firmware updates (after final product launch)	8 years
22	Minimum guaranteed availability of spare parts (after final product launch)	7 years
23	Minimum guaranteed product support (after final product launch)	7 years
24	Power supply type	External
	I .External standardised power supply (included in the product box)	n.a.
	i .Standard name	n.a.
	ii .Input voltage	n.a.
	iii .Output voltage	n.a.
	II .External standardised suitable power supply (if not included in the product box)	n.a.
	i .Standard name	n.a.
	ii .Required output voltage	n.a.
	iii .Required delivered current	n.a.
	iv .Required current frequency	n.a.