



Technical documentation-1/3

General description of the appliance	
	Multi-split

Outdoor side heat exchanger	
	air

Type of compressor driven	
	Vapor compression

Outdoor unit (1)	
TypeName	XCT8 4HP 38VS121181JCEE

Indoor unit (1)	
TypeName	Concealed Duct 40VD012S-8S-TEE

Indoor unit (3)	
TypeName	Concealed Duct 40VD009S-8S-TEE

Indoor side heat exchanger	
	air

Driver of compressor	
	electric motor

Outdoor unit (2)	
TypeName	- -

Indoor unit (2)	
TypeName	Concealed Duct 40VD009S-8S-TEE

Indoor unit (4)	
TypeName	Concealed Duct 40VD009S-8S-TEE

Technical documentation-2/3

Function	
cooling	Y
heating	Y

Average	
Warmer	N
Colder	N

Item	symbol	value	unit
Design load			
Cooling	Pdesignc	12.1	kW
Heating	Pratedh	12.5	kW
heating/Average	Pdesignh	8.8	kW
heating/Warmer	Pdesignh	-	kW
heating/Colder	Pdesignh	-	kW

Item	symbol	value	unit
Seasonal efficiency			
Cooling	η_{sc}	329.00	%
	SEER	8.30	-
heating/Average	$\eta_{sh(A)}$	149.80	%
	SCOP(A)	3.82	-
heating/Warmer	$\eta_{sh(W)}$	-	%
	SCOP(W)	-	-
heating/Colder	$\eta_{sh(C)}$	-	%
	SCOP(C)	-	-

Declared capacity for cooling at indoor temperature 27(19)°C and outdoor temperature Tj			
Tj=35°C	Pdc	12.10	kW
Tj=30°C	Pdc	9.03	kW
Tj=25°C	Pdc	5.89	kW
Tj=20°C	Pdc	5.67	kW
Degradation co-efficient	Cdc	0.25	

Declared Energy efficiency ratio for cooling at indoor temperature 27(19)°C and outdoor temperature Tj			
Tj=35°C	EERd	4.03	-
Tj=30°C	EERd	5.67	-
Tj=25°C	EERd	10.22	-
Tj=20°C	EERd	16.70	-

Declared capacity for heating/Average season, at indoor temperature 20 °C and outdoor temperature Tj			
Tj=-7°C	Pdh	7.75	kW
Tj=2°C	Pdh	4.72	kW
Tj=7°C	Pdh	3.86	kW
Tj=12°C	Pdh	4.26	kW
Tj=bivalent temperature	Pdh	7.75	kW
Tj=operation limit	Pdh	5.39	kW
Degradation co-efficient	Cdh	0.25	

Declared coefficient of performance/Average season, at indoor temperature 20°C and outdoor temperature Tj			
Tj=-7°C	COPd	2.86	-
Tj=2°C	COPd	3.30	-
Tj=7°C	COPd	5.86	-
Tj=12°C	COPd	7.45	-
Tj=bivalent temperature	COPd	2.86	-
Tj=operation limit	COPd	2.35	-

Bivalent temperature		
heating/Average	Tbiv	-7 °C
heating/Warmer	Tbiv	- °C
heating/Colder	Tbiv	- °C

Operation limit temperature		
heating/Average	Tol	-20 °C
heating/Warmer	Tol	- °C
heating/Colder	Tol	- °C

Electric power input in power modes other than active mode		
off mode	Poff	0.015 kW
standby mode	Psb	0.015 kW
thermostat-off mode	Pto	0.000 kW
crankcase heater mode	Pck	0.000 kW

Supplementary heater		
elbu		- kW

Capacity control		
Fixed		N
Strage		N
Variable		Y

Refrigerant		
Type		R410A
Weight		6.40 kg
Global warming potential GWP		2088 kgCO2eq

Technical documentation-3/3

Sound power level		
outdoor unit (cooling)		66 dB(A)
outdoor unit (heating)		69 dB(A)
outdoor unit (cooling)		dB(A)
outdoor unit (heating)		dB(A)
outdoor unit (cooling)		dB(A)
outdoor unit (heating)		dB(A)

Rated air flow			
outdoor unit (cooling)	elbu	5660	m3/h
outdoor unit (heating)	elbu	5660	m3/h
outdoor unit (cooling)	elbu		m3/h
outdoor unit (heating)	elbu		m3/h
outdoor unit (cooling)	elbu		m3/h
outdoor unit (heating)	elbu		m3/h

Outdoor unit dimension			
height		1235	mm
width		990	mm
depth		390	mm
weight		127	kg

Outdoor unit dimension			
height			mm
width			mm
depth			mm
weight			kg

Outdoor unit dimension			
height			mm
width			mm
depth			mm
weight			kg

Harmonised standard	EN 14511-3:2013
---------------------	-----------------

Calculation methods	PrEN 14825:2016
Measurement standards	

Contact details for obtaining more information	Carrier HVAC Equipment(Hangzhou)Co.,Ltd No.181, Weiken Street, Baiyang Block, Hangzhou Qiantang Area, Zhejiang Province, China
--	---