



Technical document

Suppliers name		a general description of the appliance	
Name	CARRIER JAPAN CORPORATION	Multi split type air conditioner	
Address	336 TADEHARA, FUJI-SHI, SHIZUOKA-KEN, JAPAN		
outdoor unit			
Type	XCT8 8HP		
name	38VT022188HTEE		
indoor unit		indoor unit(2)	
Type	4way cassette	Type	4way cassette
name	40VU018S-8S-TEE	name	40VU018S-8S-TEE
indoor unit(3)		indoor unit(4)	
Type	4way cassette	Type	4way cassette
name	40VU018S-8S-TEE	name	40VU018S-8S-TEE
indoor unit(5)		indoor unit(6)	
Type	-	Type	-
name	-	name	-
indoor unit(7)		indoor unit(8)	
Type	-	Type	-
name	-	name	-
Power consumption of cycling		Efficiency of cycling	
cooling	Pcyc	cooling	EERcyc
heating	Pcyc	heating	COPcyc
Degradation co-efficient		Degradation co-efficient	
cooling	Cdc	Heating	Cdc
	0,25		0,25
	-		-

U08



Function(indicate which function applies to the information)	
cooling	Y
heating	Y

If function applies to heating: Indicate the heating season the information relates to. Information should relate to one heating season at a time. Include at least the heating season 'Average'	
Average(mandatory)	Y
Warmer(if designated)	N
Colder(if designated)	N

Item	symbol	value	unit
Design load cooling	Pdesignc	22.4	kW
heating/Average	Pdesignh	13.7	kW
heating/Warmer	Pdesignh	x . x	kW
heating/Colder	Pdesignh	x . x	kW

Item	symbol	value	unit
Seasonal efficiency cooling	ηsc	291.0	%
heating/Average	SEER	7.35	-
heating/Warmer	ηsh(A)	175.4	%
heating/Colder	SCOP(A)	4.46	-
	ηsh(W)	x x x . x	%
	SCOP(W)	x . x x	-
	ηsh(C)	x x x . x	%
	SCOP(C)	x . x x	-

Declared capacity for cooling at indoor temperature 27(19)°C and outdoor temperature Tj			
Tj=35°C	Pdc	22.40	kW
Tj=30°C	Pdc	16.51	kW
Tj=25°C	Pdc	10.61	kW
Tj=20°C	Pdc	7.32	kW

Declared Energy efficiency ratio for cooling at indoor temperature 27(19)°C and outdoor temperature Tj			
Tj=35°C	EERd	3.62	-
Tj=30°C	EERd	5.03	-
Tj=25°C	EERd	8.91	-
Tj=20°C	EERd	13.81	-

Declared capacity for heating/Average climate, at indoor temperature 20°C and outdoor temperature Tj			
Tj=-7°C	Pdh	12.12	kW
Tj=2°C	Pdh	7.38	kW
Tj=7°C	Pdh	5.71	kW
Tj=12°C	Pdh	6.32	kW
Tj=bivalent temperature	Pdh	12.12	kW
Tj=operation limit	Pdh	10.50	kW

Declared coefficient of performance for heating/Average climate, at indoor temperature 20°C and outdoor temperature Tj			
Tj=-7°C	COPd	2.83	-
Tj=2°C	COPd	4.36	-
Tj=7°C	COPd	6.27	-
Tj=12°C	COPd	7.34	-
Tj=bivalent temperature	COPd	2.83	-
Tj=operation limit	COPd	1.70	-

Declared capacity for heating/Warmer climate, at indoor temperature 20°C and outdoor temperature Tj			
Tj=2°C	Pdh	x . x x	kW
Tj=7°C	Pdh	x . x x	kW
Tj=12°C	Pdh	x . x x	kW
Tj=bivalent temperature	Pdh	x . x x	kW
Tj=operation limit	Pdh	x . x x	kW

Declared coefficient of performance for heating/Warmer climate, at indoor temperature 20°C and outdoor temperature Tj			
Tj=2°C	COPd	x . x x	-
Tj=7°C	COPd	x . x x	-
Tj=12°C	COPd	x . x x	-
Tj=bivalent temperature	COPd	x . x x	-
Tj=operation limit	COPd	x . x x	-

Declared capacity for heating/Colder climate, at indoor temperature 20°C and outdoor temperature Tj			
Tj=-7°C	Pdh	x . x x	kW
Tj=2°C	Pdh	x . x x	kW
Tj=7°C	Pdh	x . x x	kW
Tj=12°C	Pdh	x . x x	kW
Tj=bivalent temperature	Pdh	x . x x	kW
Tj=operation limit	Pdh	x . x x	kW
Tj=-15°C	Pdh	x . x x	kW

Declared coefficient of performance for heating/Colder climate, at indoor temperature 20°C and outdoor temperature Tj			
Tj=-7°C	COPd	x . x x	-
Tj=2°C	COPd	x . x x	-
Tj=7°C	COPd	x . x x	-
Tj=12°C	COPd	x . x x	-
Tj=bivalent temperature	COPd	x . x x	-
Tj=operation limit	COPd	x . x x	-
Tj=-15°C	COPd	x . x x	-

Bivalent temperature		
heating/Average	Tbiv	-7 °C
heating/Warmer	Tbiv	x . x x °C
heating/Colder	Tbiv	x . x x °C

Operation limit temperature		
heating/Average	Tol	-25 °C
heating/Warmer	Tol	x . x x °C
heating/Colder	Tol	x . x x °C

Electric power input in power modes other than "on mode"		
off mode	Poffc	0.014 kW
standby mode	Pstbc	0.014 kW
thermostat-off mode	Ptoc	0.005 kW
crankcase heater mode	Pckc	0.005 kW

Seasonal electricity consumption		
cooling	QCE	1829 kWh/a
heating/Average	QHE/A	4299 kWh/a
heating/Warmer	QHE/B	x kWh/a
heating/Colder	QHE/C	x kWh/a



Electric power input in power modes other than "on mode"		Supplementary heater	
off mode	Poffh	0.022	kW
standby mode	Psbh	0.022	kW
thermostat-off mode	Ptoh	0.022	kW
crankcase heater mode	Pckh	0.001	kW
Capacity control(indicate one of three options)		Refrigerant	
Fixed	N	Type	R410A
strage	N	Weight	6.0 kg
variable	Y	Global warming potential	GWP 2088 kgCO ₂ eq.
Sound power level		Rated air flow	
Sound power level(outdoor/cool)	76.0	dB(A)	Rated air flow(outdoor/cool)
Sound power level(outdoor/heat)	78.0	dB(A)	9600 m ³ /h
		Rated air flow(outdoor/heat)	
		9600 m ³ /h	
		outdoor unit	
		dimension	
		height	1690 mm
		width	990 mm
		depth	780 mm
		weight	209 kg
Harmonised standard		EN14511-3 : 2013	
Calculation methods		PrEN 14825 : 2016	
Measurement standards			
Contact details for obtaining more information		Importer/Distributor in EU:	

Where the information included in the technical documentation file for a particular air conditioner model has been obtained by calculation on the basis of design, or extrapolation from other equivalent appliances, or both, the documentation shall include details of such calculations or extrapolations, or both, and of tests undertaken by suppliers to verify the accuracy of the calculations undertaken. The information shall also include a list of all other equivalent appliance models where the information was obtained on the same basis.