



Technical document

| | |
|----------------|---|
| Suppliers name | |
| Name | CARRIER JAPAN CORPORATION |
| Address | 336 TADEHARA, FUJI-SHI, SHIZUOKA-KEN, JAPAN |

| |
|--|
| a general description of the appliance |
| Multi split type air conditioner |

| | |
|--------------|----------------|
| outdoor unit | |
| Type | XCT8 8HP |
| name | 38VT008188HTEE |

| | |
|-------------|-----------------|
| indoor unit | |
| Type | Ducted |
| name | 40VD018H-8S-TEE |

| | |
|----------------|-----------------|
| indoor unit(2) | |
| Type | Ducted |
| name | 40VD018H-8S-TEE |

| | |
|----------------|-----------------|
| indoor unit(3) | |
| Type | Ducted |
| name | 40VD018H-8S-TEE |

| | |
|----------------|-----------------|
| indoor unit(4) | |
| Type | Ducted |
| name | 40VD018H-8S-TEE |

| | |
|----------------|---|
| indoor unit(5) | |
| Type | - |
| name | - |

| | |
|----------------|---|
| indoor unit(6) | |
| Type | - |
| name | - |

| | |
|----------------|---|
| indoor unit(7) | |
| Type | - |
| name | - |

| | |
|----------------|---|
| indoor unit(8) | |
| Type | - |
| name | - |

| | | | |
|------------------------------|------|------|----|
| Power consumption of cycling | | | |
| cooling | Pcyc | x, x | kW |
| heating | Pcyc | x, x | kW |

| | | | |
|-----------------------|--------|------|---|
| Efficiency of cycling | | | |
| cooling | EERcyc | x, x | - |
| heating | COPcyc | x, x | - |

| | | | |
|--------------------------|-----|------|---|
| Degradation co-efficient | | | |
| cooling | Cdc | 0.25 | - |

| | | | |
|--------------------------|-----|------|---|
| Degradation co-efficient | | | |
| Heating | Cdc | 0.25 | - |



| | |
|--|---|
| Function(indicate which function applies to the information) | |
| cooling | Y |
| heating | Y |

| | |
|--|---|
| If function applies to heating: Indicate the heating season the information relates to. Information should relate to one heating season at a time. Include at least the heating season 'Average' | |
| Average(mandatory) | Y |
| Warmer(if designated) | N |
| Colder(if designated) | N |

| Item | symbol | value | unit |
|-----------------|----------|-------|------|
| Design load | | | |
| cooling | Pdesignc | 22.4 | kW |
| heating/Average | Pdesignh | 13.7 | kW |
| heating/Warmer | Pdesignh | x, x | kW |
| heating/Colder | Pdesignh | x, x | kW |

| Item | symbol | value | unit |
|---------------------|---------|----------|------|
| Seasonal efficiency | | | |
| cooling | ηsc | 258.2 | % |
| | SEER | 6.53 | - |
| heating/Average | ηsh(A) | 164.6 | % |
| | SCOP(A) | 4.19 | - |
| heating/Warmer | ηsh(W) | x x x, x | % |
| | SCOP(W) | x, x x | - |
| heating/Colder | ηsh(C) | x x x, x | % |
| | SCOP(C) | x, x x | - |

| | | | |
|--|-----|-------|----|
| Declared capacity for cooling at indoor temperature 27(19)°C and outdoor temperature Tj. | | | |
| Tj=35°C | Pdc | 22.40 | kW |
| Tj=30°C | Pdc | 16.51 | kW |
| Tj=25°C | Pdc | 10.61 | kW |
| Tj=20°C | Pdc | 7.98 | kW |

| | | | |
|---|------|-------|---|
| Declared Energy efficiency ratio for cooling at indoor temperature 27(19)°C and outdoor temperature Tj. | | | |
| Tj=35°C | EERd | 3.22 | - |
| Tj=30°C | EERd | 4.27 | - |
| Tj=25°C | EERd | 8.22 | - |
| Tj=20°C | EERd | 12.27 | - |

| | | | |
|---|-----|-------|----|
| Declared capacity for heating/Average climate, at indoor temperature 20°C and outdoor temperature Tj. | | | |
| Tj=-7°C | Pdh | 12.12 | kW |
| Tj=2°C | Pdh | 7.38 | kW |
| Tj=7°C | Pdh | 5.98 | kW |
| Tj=12°C | Pdh | 6.66 | kW |
| Tj=bivalent temperature | Pdh | 12.12 | kW |
| Tj=operation limit | Pdh | 10.50 | kW |

| | | | |
|---|------|------|---|
| Declared coefficient of performance for heating/Average climate, at indoor temperature 20°C and outdoor temperature Tj. | | | |
| Tj=-7°C | COPd | 2.58 | - |
| Tj=2°C | COPd | 3.94 | - |
| Tj=7°C | COPd | 6.50 | - |
| Tj=12°C | COPd | 7.48 | - |
| Tj=bivalent temperature | COPd | 2.58 | - |
| Tj=operation limit | COPd | 1.55 | - |

| | | | |
|--|-----|--------|----|
| Declared capacity for heating/Warmer climate, at indoor temperature 20°C and outdoor temperature Tj. | | | |
| Tj=2°C | Pdh | x, x x | kW |
| Tj=7°C | Pdh | x, x x | kW |
| Tj=12°C | Pdh | x, x x | kW |
| Tj=bivalent temperature | Pdh | x, x x | kW |
| Tj=operation limit | Pdh | x, x x | kW |

| | | | |
|--|------|--------|---|
| Declared coefficient of performance for heating/Warmer climate, at indoor temperature 20°C and outdoor temperature Tj. | | | |
| Tj=2°C | COPd | x, x x | - |
| Tj=7°C | COPd | x, x x | - |
| Tj=12°C | COPd | x, x x | - |
| Tj=bivalent temperature | COPd | x, x x | - |
| Tj=operation limit | COPd | x, x x | - |

| | | | |
|--|-----|--------|----|
| Declared capacity for heating/Colder climate, at indoor temperature 20°C and outdoor temperature Tj. | | | |
| Tj=-7°C | Pdh | x, x x | kW |
| Tj=2°C | Pdh | x, x x | kW |
| Tj=7°C | Pdh | x, x x | kW |
| Tj=12°C | Pdh | x, x x | kW |
| Tj=bivalent temperature | Pdh | x, x x | kW |
| Tj=operation limit | Pdh | x, x x | kW |
| Tj=-15°C | Pdh | x, x x | kW |

| | | | |
|--|------|--------|---|
| Declared coefficient of performance for heating/Colder climate, at indoor temperature 20°C and outdoor temperature Tj. | | | |
| Tj=-7°C | COPd | x, x x | - |
| Tj=2°C | COPd | x, x x | - |
| Tj=7°C | COPd | x, x x | - |
| Tj=12°C | COPd | x, x x | - |
| Tj=bivalent temperature | COPd | x, x x | - |
| Tj=operation limit | COPd | x, x x | - |
| Tj=-15°C | COPd | x, x x | - |

| | | | |
|----------------------|------|--------|----|
| Bivalent temperature | | | |
| heating/Average | Tbiv | -7 | °C |
| heating/Warmer | Tbiv | x, x x | °C |
| heating/Colder | Tbiv | x, x x | °C |

| | | | |
|-----------------------------|-----|--------|----|
| Operation limit temperature | | | |
| heating/Average | Tol | -25 | °C |
| heating/Warmer | Tol | x, x x | °C |
| heating/Colder | Tol | x, x x | °C |

| | | | |
|--|-------|-------|----|
| Electric power input in power modes other than "on mode" | | | |
| off mode | Poffc | 0.014 | kW |
| standby mode | Psbcc | 0.014 | kW |
| thermostat-off mode | Ptocc | 0.005 | kW |
| crankcase heater mode | Pckc | 0.005 | kW |

| | | | |
|----------------------------------|-------|------|-------|
| Seasonal electricity consumption | | | |
| cooling | QCE | 2058 | kWh/a |
| heating/Average | QHE/A | 4574 | kWh/a |
| heating/Warmer | QHE/B | x | kWh/a |
| heating/Colder | QHE/C | x | kWh/a |



| Electric power input in power modes other than "on mode" | | | |
|--|-------|-------|----|
| off mode | Poffh | 0.022 | kW |
| standby mode | Psbh | 0.022 | kW |
| thermostat-off mode | Ptoh | 0.022 | kW |
| crankcase heater mode | Pckh | 0.001 | kW |

| Capacity control(indicate one of three options) | |
|---|---|
| Fixed | N |
| strage | N |
| variable | Y |

| Sound power level | | |
|---------------------------------|------|-------|
| Sound power level(outdoor/cool) | 76.0 | dB(A) |
| Sound power level(outdoor/heat) | 78.0 | dB(A) |

| Supplementary heater | | |
|--------------------------|------|---------|
| back-up heating capacity | elbu | 1.85 kW |

| Refrigerant | | |
|--------------------------|-----|----------------------------|
| Type | | R410A |
| Weight | | 6.0 kg |
| Global warming potential | GWP | 2088 kgCO ₂ eq. |

| Rated air flow | | |
|------------------------------|--|------------------------|
| Rated air flow(outdoor/cool) | | 9600 m ³ /h |
| Rated air flow(outdoor/heat) | | 9600 m ³ /h |

| outdoor unit | | | |
|--------------|--------|------|----|
| dimension | height | 1690 | mm |
| | width | 990 | mm |
| | depth | 780 | mm |
| weight | | 209 | kg |

| | |
|---------------------|------------------|
| Harmonised standard | EN14511-3 : 2013 |
|---------------------|------------------|

| | |
|--|-------------------|
| Calculation methods Measurement standards | PrEN 14825 : 2016 |
|--|-------------------|

| | |
|--|-----------------------------|
| Contact details for obtaining more information | Importer/Distributor in EU: |
|--|-----------------------------|

Where the information included in the technical documentation file for a particular air conditioner model has been obtained by calculation on the basis of design, or extrapolation from other equivalent appliances, or both, the documentation shall include details of such calculations or extrapolations, or both, and of tests undertaken by suppliers to verify the accuracy of the calculations undertaken. The information shall also include a list of all other equivalent appliance models where the information was obtained on the same basis.