



Technical document

U16

Suppliers name		a general description of the appliance	
Name	CARRIER JAPAN CORPORATION	Multi split type air conditioner	
Address	336 TADEHARA, FUJI-SHI, SHIZUOKA-KEN, JAPAN		
outdoor unit			
Type	XCT8 16HP		
name	38VT022188HTEE		
indoor unit		indoor unit(2)	
Type	4way cassette	Type	4way cassette
name	40VU027S-8S-TEE	name	40VU027S-8S-TEE
indoor unit(3)		indoor unit(4)	
Type	4way cassette	Type	4way cassette
name	40VU027S-8S-TEE	name	40VU024S-8S-TEE
indoor unit(5)		indoor unit(6)	
Type	4way cassette	Type	4way cassette
name	40VU024S-8S-TEE	name	40VU024S-8S-TEE
indoor unit(7)		indoor unit(8)	
Type	-	Type	-
name	-	name	-
Power consumption of cycling		Efficiency of cycling	
cooling	Pcyc	cooling	EERcyc
heating	Ppsych	heating	COPcyc
Degradation co-efficient		Degradation co-efficient	
cooling	Cdc	Heating	Cdc
	0,25		0,25
	-		-



Function(indicate which function applies to the information)	
cooling	Y
heating	Y

If function applies to heating: Indicate the heating season the information relates to. Information should relate to one heating season at a time. Include at least the heating season 'Average'	
Average(mandatory)	Y
Warmer(if designated)	N
Colder(if designated)	N

Item	symbol	value	unit
Design load			
cooling	Pdesignc	45,0	kW
heating/Average	Pdesignh	23,2	kW
heating/Warmer	Pdesignh	x , x	kW
heating/Colder	Pdesignh	x , x	kW

Item	symbol	value	unit
Seasonal efficiency			
cooling	ηsc	276,2	%
	SEER	6,98	-
heating/Average	ηsh(A)	173,8	%
	SCOP(A)	4,42	-
heating/Warmer	ηsh(W)	x x x , x	%
	SCOP(W)	x , x x	-
heating/Colder	ηsh(C)	x x x , x	%
	SCOP(C)	x , x x	-

Declared capacity for cooling at indoor temperature 27(19)°C and outdoor temperature Tj.			
Tj=35°C	Pdc	45,00	kW
Tj=30°C	Pdc	33,16	kW
Tj=25°C	Pdc	21,32	kW
Tj=20°C	Pdc	10,61	kW

Declared Energy efficiency ratio for cooling at indoor temperature 27(19)°C and outdoor temperature Tj.			
Tj=35°C	EERd	2,74	-
Tj=30°C	EERd	4,63	-
Tj=25°C	EERd	8,36	-
Tj=20°C	EERd	15,37	-

Declared capacity for heating/Average climate, at indoor temperature 20°C and outdoor temperature Tj.			
Tj=-7°C	Pdh	20,52	kW
Tj=2°C	Pdh	12,49	kW
Tj=7°C	Pdh	8,03	kW
Tj=12°C	Pdh	8,39	kW
Tj=bivalent temperature	Pdh	20,52	kW
Tj=operation limit	Pdh	21,00	kW

Declared coefficient of performance for heating/Average climate, at indoor temperature 20°C and outdoor temperature Tj.			
Tj=-7°C	COPd	2,72	-
Tj=2°C	COPd	4,09	-
Tj=7°C	COPd	6,52	-
Tj=12°C	COPd	8,47	-
Tj=bivalent temperature	COPd	2,72	-
Tj=operation limit	COPd	1,63	-

Declared capacity for heating/Warmer climate, at indoor temperature 20°C and outdoor temperature Tj.			
Tj=2°C	Pdh	x , x x	kW
Tj=7°C	Pdh	x , x x	kW
Tj=12°C	Pdh	x , x x	kW
Tj=bivalent temperature	Pdh	x , x x	kW
Tj=operation limit	Pdh	x , x x	kW

Declared coefficient of performance for heating/Warmer climate, at indoor temperature 20°C and outdoor temperature Tj.			
Tj=2°C	COPd	x , x x	-
Tj=7°C	COPd	x , x x	-
Tj=12°C	COPd	x , x x	-
Tj=bivalent temperature	COPd	x , x x	-
Tj=operation limit	COPd	x , x x	-

Declared capacity for heating/Colder climate, at indoor temperature 20°C and outdoor temperature Tj.			
Tj=-7°C	Pdh	x , x x	kW
Tj=2°C	Pdh	x , x x	kW
Tj=7°C	Pdh	x , x x	kW
Tj=12°C	Pdh	x , x x	kW
Tj=bivalent temperature	Pdh	x , x x	kW
Tj=operation limit	Pdh	x , x x	kW
Tj=-15°C	Pdh	x , x x	kW

Declared coefficient of performance for heating/Colder climate, at indoor temperature 20°C and outdoor temperature Tj.			
Tj=-7°C	COPd	x , x x	-
Tj=2°C	COPd	x , x x	-
Tj=7°C	COPd	x , x x	-
Tj=12°C	COPd	x , x x	-
Tj=bivalent temperature	COPd	x , x x	-
Tj=operation limit	COPd	x , x x	-
Tj=-15°C	COPd	x , x x	-

Bivalent temperature			
heating/Average	Tbiv	-7	°C
heating/Warmer	Tbiv	x , x x	°C
heating/Colder	Tbiv	x , x x	°C

Operation limit temperature			
heating/Average	Tol	-25	°C
heating/Warmer	Tol	x , x x	°C
heating/Colder	Tol	x , x x	°C

Electric power input in power modes other than "on mode"			
off mode	Poffc	0,018	kW
standby mode	Psbc	0,018	kW
thermostat-off mode	Ptoc	0,005	kW
crankcase heater mode	Pckc	0,005	kW

Seasonal electricity consumption			
cooling	QCE	3867	kWh/a
heating/Average	QHE/A	7346	kWh/a
heating/Warmer	QHE/B	x	kWh/a
heating/Colder	QHE/C	x	kWh/a



Electric power input in power modes other than "on mode"			
off mode	Poffh	0,025	kW
stanby mode	Psbh	0,025	kW
thermostat-off mode	Ptoh	0,025	kW
crankcase heater mode	Pckh	0,001	kW

Capacity control(indicate one of three options)	
Fixed	N
strage	N
variable	Y

Sound power level		
Sound power level(outdoor/cool)	85,0	dB(A)
Sound power level(outdoor/heat)	88,0	dB(A)

Supplementary heater		
back-up heating capacity	elbu	2,60 kW

Refrigerant		
Type	R410A	
Weight	9,0	kg
Global warming potential	GWP	2088 kgCO2eq.

Rated air flow		
Rated air flow(outdoor/cool)	16020	m3/h
Rated air flow(outdoor/heat)	16020	m3/h

outdoor unit		
dimension	height	1690 mm
	width	1290 mm
	depth	780 mm
weight		267 kg

Harmonised standard	EN14511-3 : 2013
---------------------	------------------

Calculation methods	PrEN 14825 : 2016
Measurement standards	

Contact details for obtaining more information	Importer/Distributor in EU:
--	-----------------------------

Where the information included in the technical documentation file for a particular air conditioner model has been obtained by calculation on the basis of design, or extrapolation from other equivalent appliances, or both, the documentation shall include details of such calculations or extrapolations, or both, and of tests undertaken by suppliers to verify the accuracy of the calculations undertaken. The information shall also include a list of all other equivalent appliance models where the information was obtained on the same basis.